



NOTES:

1. EVAPORATOR CABINET SERVICE ACCESS
2. CONDENSER CABINET SERVICE ACCESS.
3. TRANSPORTATION FEET (NOT REMOVABLE)
4. AV MOUNTING LOCATIONS
5. RECOMMENDED LIFTING POINTS (SPREADER BARS MUST BE USED)
6. EVAPORATOR COIL CONDENSATE DRAIN (Ø20mm PVC)
7. CONDENSER COIL CONDENSATE DRAIN (Ø20mm PVC)
8. ELECTRICAL SWITCH BOARD
9. ELECTRICAL ENTRY (1 x Ø20mm, 1 x Ø25mm)
10. AIR FILTER (50MM PLEATED, WASHABLE)- OPTIONAL
11. DUCTING OPTIONS:-  
 OPTION 1 - TOP S/A OR BOTTOM S/A  
 OPTION 2 - TOP R/A OR BOTTOM R/A  
 OPPOSITE HANDINGS FOR ALL OPTIONS

REVISION	DATE	DETAILS
REV-1	06.05.2013	GRILL IMAGE REMOVED ARROW ROTATED
REV-2	21.06.2013	TOP S/A & TOP R/A OPTIONS INCLUDED
REV-3	30.07.2013	LABEL CHANGED FROM AA TO AB VERSION
REV-4	31.07.2013	DIMENSIONS REVISED, DETAILS ADDED
REV-5	26.11.2013	NOTES UPDATED

DRAWING No.

CAG012009

REVISION	REV-5
DATE	26.11.2013

CUT SIZE	-----	SCALE	1 : 35
MATERIAL	-----	DRAWN	SP
QUANTITY	-----	APPROVED	MD

HPA012R3AB, HPA12C3AB, HPA015R3AB, HPA15C3AB  
 HPA017R3AB, HPA17C3AB

- ALL DIMENSIONS IN mm.
- GENERAL TOLERANCE ±1mm.
- DO NOT SCALE DRAWING.
- MASTER DRAWINGS ARE HELD ELECTRONICALLY. ANY COPY IS DEEMED UNCONTROLLED AND THEREFORE NOT NECESSARILY THE LATEST REVISION.
- ALL INFORMATION REMAINS THE PROPERTY OF THE COMPANY.

GENERAL ARRANGEMENT